


Hardener


HARDENER HD-1 is use as cross-linker in Urea-Formaldehyde (UF) and Melamine-Urea-Formaldehyde (MUF) resin. It regulate the pH of resin to optimize the curing process. The adhesive composition provides stable and consistence pot life, acceptable viscosity and better adhesion properties.

(V)	Improve	pre-bonding
\odot	IIIIpiove	pre-bolluling









APPLICATION

Mix into glue formulation

STORAGE

Store in dry and well ventilated place. Protect from sunlight.

PACKAGING

25kg / bag (Woven bag with plastic inlet liner)

SPECIFICATIONS

Physical State	Solid
Appearance	Clear to white crystal
pH (25°C)	1-3
Solubility	Completely soluble in water
Purity	> 99.5%

Recommend Dosage:

Depend on resin, glue formulation and production process

- i) High Formaldehyde Glue (MR Glue): 100kg resin with 0.2-0.5%.
- ii) Low Formaldehyde Glue: 100kg resin with 0.5-1.5%.